



**Be Right™**



## **Phosphax sc Phosphate analyser, Outdoor, 0.05-15 mg/L PO<sub>4</sub>-P, 2-channel, 115-230 VAC**

**Številka izdelka:**

**LXV422.99.14001 Nevarno**

EUR Cena:

Kontakt

Odprema v 1 tednu



### **The Phosphax sc online analyser provides reliable and accurate PO<sub>4</sub> measurements**

High precision process-photometer for the determination of the PO<sub>4</sub>-P content by vanadomolybdate yellow method. The measurement is using a photometer with automatic zero-compensation.

Can take one continuous sample stream coming from a sample preparation.

The analyser is equipped with an insulated enclosure for indoor and outdoor installation.

Flexible in sc system the analyser can be combined with all sensors via the SC controller.

Transparent, high quality measurement technology brings reliable values with the shortest of response times (only 5 minutes from sampling to measured value!).

Distorted measurement results are excluded.

The yellow method requires very little reagent (more than 50 % less chemicals) and therefore reduces operating costs considerably.

The complete system is installed tank-side and requires very little space.

### **Multiple measurement ranges for a variety of wastewater applications**

With detection limits as low as 0.05 mg/L and as high as 50 mg/L, the Phosphax sc phosphate analyser can be used anywhere in the wastewater treatment process, from the influent or start of the phosphorous removal process where phosphate levels may be high to the effluent where phosphate levels are at their lowest.

### **Low cost of operation with proven yellow method**

The Phosphax sc analyser determines ortho-phosphate concentration using the molybdoavanadate yellow colorimetric method which optimizes reagent consumption and helps save on operating costs.

### **Generate actionable insights from measurement data**

The Phosphax sc is Claros enabled so you can leverage the Hach Water Intelligence System to collect, manage and analyse data from your instrument.

### **Easy installation at the measurement point**

Hach's Phosphax sc phosphate analyser is designed to be installed at the measurement point (indoor and outdoor options). The housing is weatherproof and lockable for installation at the basin, even in the toughest climates. Mounting options include: wall, rail, or standing. The unit comes complete and assembled; no separate housing is required.

### **Low maintenance**

Several features make the Phosphax sc phosphate analyser easy to use and maintain:

1. Automatic cleaning at customized intervals.
  2. Automatic zero-calibration at each measuring cycle.
  3. Prognosys Predictive Diagnostics alerts you to upcoming instrument issues and guides you on whether the changes in your measurements are due to your instrument or your water.
  4. Easy access to reagents and wear parts.
- 

## Specifikacije

Channels:	2
Delovna temperatura:	-20 - 45 °C
Dimenzija (v x š x g):	720 mm x 540 mm x 390 mm
Dolžina kabla:	2 m fixed data cable at analyser
Frekvenca (Hz):	50/60 Hz
Garancija:	24 mesecev
Izhod:	Current output, relays and bus communication via SC controller
Kakovost vzorca:	Ultra filtrated or comparable
Material:	ASA/PC UV-resistant
Meja zaznavanja:	0.05 mg/L PO <sub>4</sub> -P
Merilna metoda:	Photometric method using vanadate-molybdate
Merilni interval:	5 - 120 min, adjustable per 5 min.
Merilno načelo:	Phosphate ions react with vanadate-molybdate reagent to form a yellow dye.
Merilno območje:	0,05 - 15,0 mg/L PO <sub>4</sub> -P
Možnosti podajanja vzorca :	Outdoor
Možnosti vzorčenja:	2-channel continuous sample from filtration unit, e.g. Filtrax
Način premora:	115-230 VAC
Napetost (V):	115 - 230 V AC, napajno s Power Box-om ali z SC Controller
Natančnost:	± 2 % ± 0,05 mg/L
Območje tlaka:	-30 - 50 mbar with continuous sample preparation; at overflow vessel
Obnovljivost:	2 % + 0,05 mg/L
Odzivni čas :	< 5 minutes
Parameter:	ortho-Phosphate
Permissible Chloride range:	Max. Cl <sup>-</sup> concentration: 1000 mg/L
pH območje:	5 - 9 pH
Pogoji skladiščenja:	-20 °C - 60 °C
Poraba reagenta:	500 mL/month
Prenos podatkov:	Current output, relays and bus communication via SC controller
Pretok:	1 - 20 L/h sample (free of suspended solids)
Sistem filtrov vključen:	Ne, uporabite npr. Filtrax
Št. kanalov:	2
Stopnja vzorca:	Level of liquid in basin with filtration probe must be below analyser
Temperatura vzorca:	4 - 40 °C
Teža:	Without sample preparation system and without chemicals: 31 kg
V zaprtih prostorih/Na prostem:	Na prostem

Vrsta ohišja:	Outdoor
Vsebina paketa:	0.05 - 15 mg/L PO <sub>4</sub> -P, 230 VAC Phosphax sc Ortho-Phosphate Analyser, outdoor version, 2-channel continuous sample from filtration unit, 3 month supply of all necessary consumables at 5 minute cycle time, user manuals
Zaščita ohišja:	IP55
Zaščita varovalke:	Via SC1000 controller or power box. Maximum of 2 analysers per SC1000 or power box

---

## Vsebina paketa

0.05 - 15 mg/L PO<sub>4</sub>-P, 230 VAC Phosphax sc Ortho-Phosphate Analyser, outdoor version, 2-channel continuous sample from filtration unit, 3 month supply of all necessary consumables at 5 minute cycle time, user manuals

---

## Obvezni pripomočki

- Sondni modul SC1000 za 4 senzorje, 4 izhodi 4 - 20 mA, rele, 110 - 240 V AC, kabel za EU (Item LXV400.99.2R121)
- Zaslonski modul SC1000 (Item LXV402.99.00001)
- Kontrolna enota SC4500, Prognosys, 5 izhodov mA, 2 digitalna senzorja, brez vtiča (Item LXV525.99A11551)
- Kontrolna enota SC4500, podpora za Claros, 5 izhodov mA, 2 digitalna senzorja, brez vtiča (Item LXV525.99AA1551)
- Kontrolna enota SC4500, podpora za Claros, 5 izhodov mA, 2 digitalna senzorja, vtič za EU (Item LXV525.99CA1551)