




Flow through unit Nitratax clear sc, 5 mm

Številka izdelka: **LZX866**

EUR Cena: Kontakt

Odprema v 1 tednu

The through-flow variant is used wherever direct measurement in the medium is not possible for construction related reasons or the medium load makes it necessary to measure a filtered sample.

Specifikacije

Delovna temperatura:	2 - 40 °C (sample temperature)
Dimenzija (v x š x g):	210 mm x 500 mm x 160 mm
Material:	Measuring cell: PVC;
	Glands: PVDF;
	Sample tube: PVC;
	Screws: Stainless Steel;
	Seals: EPDM
Materiali v stiku z vodo:	Measuring cell: PVC;
	Seals: EPDM;
	Glands: PVDF;
	Sample tube: PVC
Območje tlaka:	Not pressurized, open drain
Prostornina vzorca:	0,5 - 10 L
Teža:	3,6 kg
Vhod vzorca:	Tube ID 4 mm/AD 6 mm