



AS950 All Weather Refrigerated Sampler, 230 V, with heater, 1 - 10 L Bottle

Številka izdelka: ASA.CXXX4X21XX

EUR Cena: Kontakt

Datum pošiljanja ni prikazan

Sampling has never been this easy.

The AS950 All-Weather Refrigerated Sampler is the perfect solution for easy and reliable sample collection in all conditions. With its specially designed air-sensing thermostat, it preserves samples regardless of outside temperatures and conditions, ensuring that your samples are safe and accurate.

In addition to its advanced temperature control, the AS950 All-Weather Refrigerated Sampler features a large, full-color display, intuitive single-screen programming, and USB data transfer capabilities that simplify and streamline the entire sampling process. You can even copy programs from sampler to sampler, eliminating tedious programming and saving time.

Investing in the AS950 All-Weather Refrigerated Sampler gives you the easiest and most intuitive operation, the most convenient data transfer and programming, and the confidence in your sampling process you need, no matter what the weather. Order yours today and simplify your sampling process.

Easiest and most intuitive operation

The large full colour display and intuitive programming give you access to all your programmable criteria on a single screen - eliminating scrolling through menus and supporting error-free operation.

Most convenient data transfer and programming available

The AS950 is the only sampler that utilises a USB drive to upload and download data and copy programs from one sampler to another.

Confidence in your sampling process

The program status screen instantly communicates alarms, missed samples and program progress for quick and easy troubleshooting.

Resists corrosion

The All-Weather Refrigerated (AWR) sampler base is designed to endure humid and highly corrosive environments, minimising damage caused by corrosive gases, rodents, and standing water to guarantee environmental integrity.

Accurate and consistent sample preservations

The custom-designed air-sensing thermostat controls temperature in accordance with USEPA and international guidelines, preserving samples regardless of outside temperatures and conditions.

Specifikacije

Alarm:

Configurable alarms that show on status screen and are recorded in diagnostics alarm logs. Alarms can be set for system diagnostics and logging such as program end, sample complete, missed samples and full bottle. Channel alarms are setpoint alarms for the recorded measurements (channels), such as pH, level and power supply voltage.

Automatic shutdown:	Multiple Bottle Mode: After complete revolution of distributor arm (unless Continuous Mode is selected)
	Composite Mode: After preset number of samples have been delivered to composite container, from 1 to 999 samples, or upon full container.
Base Configuration:	230V base w/heater and lock, EU
Beleženje podatkov:	SAMPLE HISTORY - Stores up to 4000 entries for sample time stamp, bottle number and sample status (success, bottle full, rinse error, user abort, distributor error, pump fault, purge fail, sample timeout, power fail and low main battery).
	MEASUREMENTS - Stores up to 325,000 entries for selected measurement channels in accordance with the selected logging interval.
	EVENTS - Ability to store up to 2000 entries in Sample History logging. Records Power On, Power Fail, Firmware Updated, Pump Fault, Distributor Arm Error, Low Memory Battery, Low Main Battery, User On, User Off, Program Started, Program Resumed, Program Halted, Program Completed, Grab Sample, Tube Change Required, Sensor Communication Errors, Cooling Failed, Heating Failed, Thermal Error Corrected.
Bottle Set:	Composite 10 L polyethylene bottle kit
certificiranje:	CE, UL, CSA
Certificiranje:	CE, UL
Diagnostika:	View event and alarm logs as well as maintenance diagnostics
Dimenzija:	76 cm x 81 cm x 130 cm
Factory Installed Options:	RAIN/RS485 PORT
	Accepts Hach Rain Gauge (not included) or can be used as RS485 communications
Frekvenca (Hz):	50 - 60 Hz
Funkcija zaklepanje zaslona:	Access code protection prevents tampering
Garancija:	24 mesecev
Hladilni sistem:	Top mounted compressor and fan-forced air cooled condenser; 11/5 HP 115 VAC: 115 °C thermal overload protector, 7.1 locked rotor amps; 230 VAC: 120 °C thermal overload protector, 7.6 A peak start current; 3-sided wraparound plate type evaporator; Rigid foam insulation: 7.6 cm sides, 12.7 cm top, 15.2 cm bottom; Lockable lid to prevent tampering with programming; Recovery Time: Sampler temperature recovers to 4 °C within 5 minutes after door has been held open for one minute in 24 °C ambient environment while in an active cooling cycle; Pull Down Time: from 24 °C to 4 °C , 20 minutes; Temperature Control: 4 °C (±0.8 °C)
Internal clock:	±1 second per day at 25 °C
Interval vzorca:	Selectable in single increments from 1 to 9999 flow pulses or 1 to 9999 minutes in one minute increments
jeziki:	English, French, Spanish, Italian, German, Portuguese, Chinese
Jeziki uporabniškega vmesnika:	Chinese, English, French, German, Italian, Spanish, Portuguese
Komunikacija:	USB and optional RS485 (Modbus)
Manual sampling:	Initiates a sample collection independent of program in progress
Material ohišja:	IP24, low-density Polyethylene with UV inhibitor (Sampler)
Način delovanja:	Continuous or non-continuous
Način premora:	230 V
Način vzorčenja:	Pacing: Time weighted, Flow weighted, Time table, Flow table, Event
	Distribution: Single bottle composite, multi-bottle composite, multi-bottle discrete, bottles per sample, samples per bottle or a combination of bottles per sample and samples per bottle
Napetost (V):	230 V

Natančnost prostornine vzorca:	Typical: ±5% of 200 mL sample volume with: 4.6 m vertical lift, 4.9 m of 3/8" Vinyl intake tube, single bottle, full bottle shut-off at room temperature and 1524 m elevation
Port senzorja:	No
Posebna značilnost:	With Heater and Lock
Posoda z vzorcem:	1 x 20 L
Programs:	Dual Programs: Up to 2 sample programs can be run sequentially, in parallel, or according to day of week scheduling; enabling a single sampler to function like multiple samplers
Prostornina vzorca:	Programmable in 10 mL increments from 10 - 10,000 mL
Pump flow rate:	4.8 L/min at 1 m vertical lift with 3/8" intake tube typical
Rain gauge input:	Ne
Refrigeration components and plumbing:	Corrosion protected with conformal all exposed copper tubing is insulated to avoid sweating and condensation
Sample pump:	High-speed peristaltic, dual roller, with 0.95 ID x 1.6 OD cm (3/8" ID x 5/8" OD) pump tube; Pump body IP37, Polycarbonate cover
Sample transport velocity:	0.9 m/s with 4.6 m vertical lift, 4.9 m of 3/8" Vinyl intake tubing, 21 °C and 1524 m elevation
Sample trigger:	When equipped with flow sensor or pH/temperature sensor or peripheral monitoring options, sampling can be triggered upon an upset condition when field selectable limits are exceeded
Sample volume repeatability:	Typical: ±5% of 200 mL sample volume with: 4.6 m vertical lift, 4.9 m of 3/8" Vinyl intake tube, single bottle, full bottle shut-off at room temperature and 1524 m elevation
Senzor:	None
Sonde vključene:	No
Spomin:	Sample history: 4000 records; Data log: 325,000 records; Event log: 2000 records
Status messages:	Communicates what program is running, if there are any missed samples, when the next sample will be taken, how many samples remain, number of logged channels, time of last measurement, memory available, number of active channels, if alarms were triggered, when alarms were triggered, active sensors and cabinet temperature
Suction Hose Outer Diameter:	1/4" and 3/8" ID PTFE-lined Polyethylene with protective outer cover available in clear and black.
Temperatura:	Operating: AWRS: 0 - 50 °C AWRS with optional controller compartment heater: -40 - 50 °C AWRS with controller compartment heater and AC battery back up: -15 - 40 °C Storage: -30 - 60 °C
Teža:	86 kg
Tip osnove:	With controller compartment heater
Tubing:	Pump tubing: 9.5 mm ID x 15.9 mm OD Silicone Intake tubing: 1.0 - 4.75 m minimum length, 1/4" or 3/8" ID Vinyl or 3/8" ID PTFE-lined Polyethylene with protective outer cover (black or clear)
User interface:	Membrane switch keypad with 2 multiple function soft keys
Vertical lift:	8.5 m using 8.8 m maximum of 3/8" Vinyl intake tube at sea level at 20 to 25 °C
Vhodi:	One 0/4-20 mA input for flow pacing
Vhodno izpiranje:	Strainers: Choice of PTFE and 316 stainless steel construction, or all 316 stainless steel in standard size, high velocity, and low profile for shallow depth applications

Purge: Air purged automatically before and after each sample;

duration automatically compensates for varying intake line lengths

Rinse: Intake line automatically rinsed with source liquid prior to each sample, from 1 to 3 rinses

Retries or Fault: Sample collection cycle automatically repeated from 1 to 3 times if sample not obtained on initial attempt

Vsebina paketa:

1 ea. AS950 controller on 230 V All Weather base with controller compartment heater

1 ea. Bottle kit (AW010030), includes 1 x 10 L PE bottle w/cap (1918), composite tube support (8838) and full bottle shut-off (8847)

1 ea. 7 m vinyl intake tubing (920)

1 ea. strainer (926)

Zaslon: LCD (osvetlitev iz ozadja):

1/4 VGA, Colour; self-prompting/menu-driven program

Vsebina paketa

1 ea. AS950 controller on 230 V All Weather base with controller compartment heater
1 ea. Bottle kit (AW010030), includes 1 x 10 L PE bottle w/cap (1918), composite tube support (8838) and full bottle shut-off (8847)
1 ea. 7 m vinyl intake tubing (920)
1 ea. strainer (926)