



Acidification/Cleaning Unit for Amperometric Sensors

Številka izdelka: **LZY051**
EUR Cena: Kontakt
Odprema v 2 tednih

Many amperometric processes have optimal pH ranges in which they will be most accurate and produce the best results. Adding an acidification/cleaning unit onto instruments such as the CL10 sc can help to ensure that samples stay range that is favorable for measurement.

Specifikacije

Depth panel:	107 mm
Dolžina kabla:	1 m digital
Garancija:	24 mesecev
Height (panel):	270 mm
Material:	Carboy: PEHD (high-density polyethylene)
Napetost (V):	12 V DC
Obseg:	10 L chemicals not supplied
Pretok:	Min 0.24, max. 1 mL/min
Procesni priključek:	0.125 " NPT (for tube fittings)
Razred varovalke:	T, 250 mA, 250V
Vsebina paketa:	Acidification Unit, Carboy, 1 M digital extension cable, Tubing Kit, and Instructions.
Width:	250 mm

Vsebina paketa

Acidification Unit, Carboy, 1 M digital extension cable, Tubing Kit, and Instructions.