



Polymetron 8398.3 Inductive conductivity sensor, DN 50 version

Številka izdelka: 08398=A=3000

EUR Cena: Kontakt
Odprema v 2 tednih

Flow through probe, Polyetheretherketone (PEEK), with 5 m cable, runs with controller Monec 9135 and SI792

High chemical and mechanical resistance

Accuracy over a wide measuring range

Perfect compact sanitary design for 2"/DN50 access port in compliance with 3A standards

Maintenance free: No electrode damage, no polarisation effect

Versatile mounting options: flow-through adapters and chambers, immersion shafts

Specifikacije

Delovna temperatura:	140 °C maximum
Dolžina kabla:	5 m fixed cable
konstanta celice k:	2.35
Material:	PEEK
Materiali v stiku z vodo:	PEEK
Merilno načelo:	Inductive conductivity measurement
Merilno območje:	0,2 - 2000 mS/cm
Območje tlaka:	Najv. 18 bar
Ponovljivost:	< ± 2 % ali ± 0.004 mS/cm, kar je večje
Tesnilo:	2 " EPDM gasket
Teža:	0,700 kg

Obvezni pripomočki

- Kontrolna enota SC4500, Prognosys, 5 izhodov mA, 2 digitalna senzorja, brez vtiča (Item LXV525.99A11551)
- Kontrolna enota SC4500, podpora za Claros, 5 izhodov mA, 2 digitalna senzorja, brez vtiča (Item LXV525.99AA1551)
- Kontrolna enota SC4500, podpora za Claros, 5 izhodov mA, 2 digitalna senzorja, vtič za EU (Item LXV525.99CA1551)