



Digital extension cable for SC sensors, 0.35m

Številka izdelka: **LZX847**
EUR Cena: Kontakt
Na voljo

Specifikacije

Delovna temperatura:	0 - 80 °C Fixed Installation
Dolžina kabla:	0.35 m
Izolacijski upor:	$\geq 20 \text{ M}\Omega \times \text{km}$ at 20 °C
Kodiranje žice:	AWG 22: brown (+12V DC) Black (circuit common) AWG 26: white (data -) blue (data +)
Material:	CU: AWG 22 - 19×0.15mm AWG 26 - 18×0.10mm
Minimal bend radius:	7.5 x outer diameter, flexible installation
Minimal bend radius 2:	5 x outer diameter, fixed installation
Normalna napetost:	250 V Vpp
Outside coat:	PUR (Elastoplan 1185), RoHS-conformal
Premer, zunanji:	6.8 mm $\pm$ 0.3 mm
Shield attenuation:	$\geq 55 \text{ dB}$
Skupna zaščita:	Cu netting, tinned
Testna napetost:	750 V Vrms wire/shield
Upor vala:	ca. 95 Ω at 1kHz, AWG 22 pairs

Upor žice:

max. 106 Ω /km AWG 22 at 20° C (loop)