



Digital extension cable for SC sensors, 30 m

Številka izdelka: LZX852
EUR Cena: Kontakt
Datum pošiljanja ni prikazan

Specifikacije

Delovna temperatura:	- 80 °C Fixed Installation
Dolžina kabla:	30 m
Izolacijski upor:	$\geq 20 \text{ M}\Omega \times \text{km}$ at 20 °C
Kodiranje žice:	AWG 22: brown (+12 V DC) Black (circuit common) AWG 26: white (data -) blue (data +)
Material:	Cable: Cu: AWG 22 - 19×0.15 mm AWG 26 - 18×0.10 mm
Minimal bend radius:	7.5 × outer diameter, flexible installation
Minimal bend radius 2:	5 × outer diameter, fixed installation
Normalna napetost:	250 V Vpp
Outside coat:	PUR (Elastoplan 1185), RoHS-conformal
Premer, zunanji:	6.8 mm ± 0.3 mm
Shield attenuation:	$\geq 55 \text{ dB}$
Skupna zaščita:	Cu- netting, tinned
Testna napetost:	750 V Vrms wire/shield
Upor vala:	ca. 95 Ω at 1 kHz, AWG 22 pairs

Upor žice:

max. 260 Ω /km AWG 26 at 20 °C (loop)