



## Test kit, silica, model SI-5

Številka izdelka: 1455400

EUR Cena: Kontakt

Na voljo

Nearno



Dissolved silica is found in almost all natural waters. Its presence is undesirable for many industrial uses because of scale formation. High-pressure boiler turbines are especially susceptible. This simple, low-cost color disc method is the most accurate visual test kit method.

**Popular in many industrial applications, such as boiler turbines that are susceptible to scale**

**Provides fast results with an easy-to-carry test kit**

**Simple, low-cost color disc method is the most accurate visual test kit method**

---

### Specifikacije

Ime metode:	Color disc/  Heteropoly blue  amino acid
Merilno območje:	0 - 600 mg/L SiO <sub>2</sub>
Model:	SI-5
Parameter:	Silica
Platforma:	Color Disc
Smallest increment:	1  20
Standardno merilno območje:	0 - 30 mg/L SiO <sub>2</sub> ; 0 - 600 mg/L SiO <sub>2</sub>
Število testov:	100
Test Kit model:	SI-5
Vrsta primera:	D