



Sigma SD 900 Portable sampler, 1x 11.4L PE, 230V, EU plug

Številka izdelka:

SD900P.99.11112

ZASTAREL IZDELEK
Ta izdelek ni več na voljo.

Portable, practical and rugged: Sigma SD 900

Before and after each sampling operation, an automatic air-purge is carried out. In addition, the intake line can be rinsed several times with the source liquid before sampling is carried out. There is therefore no chance of carryover occurring.

Up to 20 times longer service life: The newly designed peristaltic pump has spring-mounted rollers. Large particles and solids therefore do not interfere with the sampling and virtually no wear occurs. The pump housing is transparent, so visual checks can be carried out at any time.

The compact sampler is easy to transport, freely programmable and extremely flexible, thanks to the variable container options.

Easy to operate, with intuitive user guidance

implified keypad with intuitive icons and scrolling menu of the Hach Sigma SD900 Active Cooling Sampler assures easy setup. The large 5-line transreflective LED backlit display is readable in bright or subdued lighting.

Reduced maintenance through spring-mounted peristaltic pump

Worried about replacing tubing? The peristaltic pump with spring loaded rollers reduces pump tubing wear and prevent pump jams. The life time of pump tubing is 20,000 cycles compared to 1000 cycles on other samplers.

Fast programming and updates by computer

Do you need samples to meet local regulations of 24 x hourly mixed / daily mixed sample?

We offer unique options of 1 x 25 liter PE and 1 X 20 liter glass with an active cooled sampler base.

Repeated rinsing avoids cross-contamination

The compact, weather-proof housing polyethylene plastic ensures failure-free operation over many years even in extremely corrosive applications.

Accurate sampling for correct analysis

The Sigma SD900 Portable Active cooling sampler comes with an integrated cooling machine which includes an autarktic temperature control for accurate temperature controlled sample conservation.

Specifikacije

Garancija:	24 mesecev
Možnosti:	1x 11.4 L PE
Način premora:	EU plug
Prostornina vzorca:	Nastavljena po korakih za 10 ml od -
Razpršena svetloba:	pri 4,6 m navpičnega dviga po 4,8-metrski vinilni dovodni cevi s premerom 0,95 m (3/8 palca) na nadmorski višini 0 pri 2 °C

Sesalna višina:

Vsaj sesalna glava pri 8,84-metrski vinilni dovodni cevi premera 0,95 m (3/8 palca) na nadmorski višini 0 med 20 in 25 °C