



HQ11D Digital pH meter kit, pH electrode, liquid, Std., 1m

Številka izdelka:

HQ11D.99.151000

ZASTAREL IZDELEK

Ta izdelek ni več na voljo.

Digital Electrochemistry with HQD

Portable pH/ORP meter. Instrument with Standard pH electrode, liquid, cable length 1m.

The digital meter/electrode system combines reliability, flexibility and ease of use. Interchangeable Intellical electrodes are recognised automatically and store all relevant data. Rugged, nearly indestructible outdoor versions with multiple cable lengths enable measurements even at previously inaccessible locations.

Replaced by NEW HQ Series.

Outstanding reliability and simple handling

Versatile electrodes for all applications, e.g. wastewater, drinking water, process water

Reliable results from inaccessible measurement locations and over long distances - even for pH

Full GLP data management

Competent support through innovative technology and comprehensive applications know-how

Specifikacije

AC in USB delovanje:	Optional
Delovna sporočila o napakah:	Clear text error messages displayed
Delovni pogoji: relativna vlažnost zraka:	90 % relative humidity (non-condensing)
Delovni pogoji: temperatura:	0 - 60 °C (32 - 140 °F)
Delovni vmesnik:	Soft Touch Keypad
Določen izbor pufrov:	Color-coded: 4.01, 7.00, 10.01 pH; IUPAC: 1.679, 4.005, 7.000, 10.012, 12.45 DIN: 1.09, 4.65, 9.23 User-defined custom buffer sets
Funkcija zaklepanje zaslona:	Continuous / Auto-stabilization ("press to read") / At Interval
Garancija:	36 mesecev
GLP značilnosti:	Date; Time; Sample ID; Operator ID

Inštrument:	Portable
IP ocena ohišja:	IP67
Izvoz podatkov:	Download via USB connection to PC or flash memory device. Automatically transfer entire data log or as readings are taken. Power supply adapter required.
jeziki:	English, German, French, Italian, Spanish, Danish, Dutch, Polish, Portuguese, Turkish, Finnish, Czech, Russian.
Merilna metoda:	Probe specific programmed method settings
Meritev temperature:	-10 - 110 °C
Model:	HQ11D – pH/1 Channel
mV meritev :	-1500 - 1500 mV
mV meritev pri stabilnem odčitavanju:	Yes
mV resolucija:	0.1 mV
Obseg dobave:	Meter package includes HQ11D Portable Meter; 4 AA batteries; PHC301 Standard Gel pH Electrode, 1 m cable; Singlet™ pH 4 & 7 Buffer pouches 10 of each; quick-start guide and user manuals.
Parameter:	pH/Oxydo Reduction Potential (ORP)
Parameters:	pH
	NA
	NA
PC data transfer software :	HQD Series Meter Data Transfer Utility
pH Electrode calibration:	1 - 3 Calibration points
	Calibration summary data logged and displayed
pH Measurement Range:	0 - 14 pH
pH resolucija:	Možnost izbire med 0.001 - 0.1 pH
Pomnilnik podatkov:	Automatic, GLP ISO compliant reading data stored with batteriescalibration details.
Pomnilnik/hranjenje podatkov:	500 records/FIFO
Posebni kalibracijski standardi:	Yes
Potrdila o skladnosti:	CE.WEEE
Printer:	Yes, Optional
Samodejno prepoznavanje pufra:	Yes
Sensor A:	PHC30101 (1 m)
Sensor B:	NA
Sensor C:	NA
Sensors:	Sensor A: PHC30101
	Sensor B: NA
	Sensor C:
Sestava:	No
Set?:	Da
Sonde vključene:	PHC30101
Temperaturna kompenzacija:	Samodejna temperaturna kompenzacija za pH
Temperaturna natančnost:	± 0.3 °C
Temperaturna resolucija:	0,1 °C
Teža:	339 g (0.75 lb) without batteries; 430 g (0.95 lb) with batteries
Type of measurement:	Field Measurements

Umeritveni intervali/alarmi/opomniki:	Izklopljeno, izbira od 2 uri do 7 dni
Umerjenje ORP elektrode:	Predefined ORP standards (including Zobell's solution)
Vhodi:	1
Vrsta sonde:	Intellical Digital SMART Standard Laboratory or Rugged Field
Vrsta zaslona:	240 x 160 pixel LCD with batteriesbacklight illumination
Vsebina paketa:	Meter package includes HQ11D Portable Meter; 4 AA batteries; PHC301 Standard Gel pH Electrode, 1 m cable; Singlet pH 4 & 7 Buffer pouches 10 of each; quick-start guide and user manuals.
Zaslon: LCD (osvetlitev iz ozadja):	Detailed mode/Large mode

Vsebina paketa

Meter package includes HQ11D Portable Meter; 4 AA batteries; PHC301 Standard Gel pH Electrode, 1 m cable; Singlet pH 4 & 7 Buffer pouches 10 of each; quick-start guide and user manuals.