



## **EZ9010 Filtration System, for immersion, pore size 50 µm, 3 m tubing**

Številka izdelka:

**EZ9010.XX310A01**

**ZASTAREL IZDELEK**  
Ta izdelek ni več na voljo.

### **Universal self-cleaning filtration systems - compatible with all EZ Series online analysers**

#### **About the EZ9000 Series**

The successful implementation of online analysers in process control strategies could not have been achieved without the development of a new generation of automatic sampling and sample preconditioning systems. The EZ9000 Series are the result of many years of field experience in combining analysers with filtration units.

#### **Simplified operation by self-cleaning action**

All preconditioning systems are designed for fully automatic operation and require virtually no human intervention. Basically all systems are incorporated either with a blowback action by instrument air, or a specific cleaning cycle. This fundamental design principle does not merely allow trouble-free sampling, moreover it contributes to high uptimes.

The EZ9010 systems are front runners of the filtration series and the standard designed for reliably delivering filtered samples to an online analyser. The self-cleaning feature of the unit includes a blowback action with sample to prevent the filter element, the sample tubing and the analyser from blocking and blinding. Prime features include:

- Self-cleaning sample filtration with various pore sizes
- Automatic cleaning action: blowback by solenoid controlled instrument air
- Static Pressure Regulator assures a constant, readily available sample level at atmospheric pressure
- PLC or analyser controlled cleaning frequency

---

### **Specifikacije**

Cleaning:	Automatic blowback by solenoid controlled instrument air
Dimenzija (v x š x g):	750 mm x 550 mm x 200 mm
Earth connection:	Dry and clean earth pole with low impedance (< 1 Ohm) using an earth cable of > 2.5 mm <sup>2</sup>
Instrument air:	Dry and oil free according to ISA-S7.0.01-1996 quality standard for instrument air
Material:	Filter: SS 316L
	Piping: PVC
	Manual ball valves: PVC

	Tubing: Norprene, PFA, PE
	Static Pressure Regulator: PMMA
	Panel: weather resistant Trespa
Moč:	24 VDC, powered by analyser or external supply
Odvod:	Sample return line 1" BSF; overflow Static Pressure Regulator 3/8" OD
Posebna značilnost:	Immersion Version
Posebni zapiski:	Backflush valve controlled by Analyzer
Razred zaščite:	IP55
Required fast loop:	2 m/s
Size:	50 µm
Št. vzorca:	1 stream
Temperatura vzorca:	Max. 65 °C
Teža:	12 kg
Tubing:	Up to 3 m

Optional:

up to 3 m with heating

up to 6 m

up to 6 m with heating

up to 10 m

up to 10 m with heating

up to 15 m

up to 15 m with heating

up to 20 m

up to 20 m with heating

Velikost por: 50 µm

Optional:

100 µm, 200 µm